

A background image showing a man with glasses and a red shirt working on a piece of industrial machinery. The machinery is metallic and has various components, including a vertical shaft and a horizontal arm.

# 尖端的真空设备 凯旭产品选型手册

姓名:陈强

微信:kaixuvc

电话:132-6865-5599

邮箱:chenqiang@kaixuvc.cn

网址:www.kaixuvc.com

地址:东莞市寮步镇寮步坑口振兴四巷3号

营业联系



# XDD1干式隔膜泵



D-LAB膜泵：用这些高品质机器支持您的化学或制药实验室运营。这些泵采用耐化学特氟龙®头、隔膜和Kalrez®阀门设计，提供多种选择。

Edwards系列D-Lab隔膜泵提供清洁泵，设计轻巧紧凑，非常适合多种实验室应用。泵可以独立运行，维护需求极少。D-Lab泵包括单头和双头泵，抽水速度最高可达2立方米/小时。

选择单头、100 mbar终极真空泵用于干燥设备或水射流泵更换。另外，双头8毫巴终极真空泵非常适合旋转蒸发、气体转移及各种中真空应用。

## 产品特点

干式泵送、无润滑剂技术——免除了昂贵的换油和处理。


轻便紧凑——体积小，使用灵活。

理想的备份泵——适用于小型涡轮分子泵。

符合 EN61010 、 EN1012 、 CSA/UL标准。

全球范围内——115/230 V或24 V可选。

IEC 60320 C13连接器——用于交流泵。



# 24小时为客户提供服务

高效率

高品质

高服务

除了拥有出色的性能、效率及实用性的真空设备，我们也可以提供精湛的服务和支持。无论是在我们的服务中心还是您的现场，我们均可为多个品牌和应用提供服务。可以快速响应您的需求，就算是不间断工艺，也可让您安心生产。

In addition to vacuum equipment with excellent performance, efficiency, and practicality, we can also provide exquisite servicesService and support. Whether in our service center or on your site, we can serve multiple brands and applicationsProvide services. We can quickly respond to your needs, even with uninterrupted processes, allowing you to produce with peace of mind.

## 你想了解更多吗？

请直接联系我们！

电话：132-6865-5599

邮箱：chenqiang@kaixuvac.cn



在线客服



营业联系